



# GD2126TN, Mech Ground, 2 Cables to Rod or Pipe, Tin Plated

By Burndy  
Catalog # [GD2126TN](#)



2 Copper Cables to Rod, Pipe, or Column, Accommodates 3-1/2" to 4" IPS, 3-1/2" Rod, #4 Sol-2/O Str Copper, Direct Burial

## Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

## Specifications

|                                         |                      |
|-----------------------------------------|----------------------|
| Certification - ETL                     | No                   |
| Certification - UL Recognized           | No                   |
| Standards - RoHS Compliance             | EX                   |
| Status                                  |                      |
| Certification - cULus                   | No                   |
| Certification - UL Listed Direct Burial | Yes                  |
| Buy America(n) Qualified                | Contact Manufacturer |
| UL Listed                               | Yes                  |
| Certification - CSA Approved            | No                   |

## Dimensions

|                |          |
|----------------|----------|
| Package Height | 0.000 in |
|----------------|----------|

|                        |           |
|------------------------|-----------|
| Package Weight         | 0.000 lb. |
| Dimension - Width inch | 5.31 in   |
| Package Length         | 0.000 in  |
| Package Width          | 0.000 in  |

## General

|                   |                    |
|-------------------|--------------------|
| Plated            | N                  |
| UPC               | 781810502754       |
| U Bolt Type       | 264                |
| Material          | Copper Alloy, Cast |
| Plating Type      | Tin Plated         |
| UPC 12 Digit      | 781810502754       |
| UPC 14 Digit GTIN | 00781810502754     |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 3 |
|-----------------------|---|

## Product Assets

[Catalog \[English\]](#)