



GD2226, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD2226](#)

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 4" to 4-1/2" Rod, 4" Pipe

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor Size	#4 Sol AWG - 2/0 Str AWG
Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Solid Size Range	4-2/0
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG
Conductor - Copper Str Size B Range	4



Conductor - Copper Tube Std Size Range	4
Conductor - Copper Tube Std Size	4

Dimensions

Package Height	0.000 in
Dimension - Height mm	162.1 mm
Dimension - Height inch	6.38 in
Dimension - Height fraction	6-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width fraction	5-7/8 in
Dimension - Width mm	148 mm
Dimension - Width inch	5.81 in
Dimension - B Length inch	1.63 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810260463
Type	GD
U Bolt Type	261
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260463
UPC 14 Digit GTIN	00781810260463

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)



A Hubbell brand