



GD8629, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GD8629](#)



2 Parallel Cables to Rod or Pipe, Accommodates 2/0 AWG Sol-250 kcmil, 6" to 6-5/8" Pipe

Features

- 2 Parallel Cables to Rod or Pipe
- 2/0 AWG Sol to 250 kcmil
- 6" to 6-5/8" Pipe

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	2/0 AWG Sol - 250 kcmil
Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 2/0 • 3/0 • 4/0 • 250

Conductor - Copper Str Size B Range 6

Dimensions

Dimension - Pad Width inch	5.81 in
Package Height	0.000 in
Dimension - Height mm	211.1 mm
Dimension - Height inch	8.31 in
Package Weight	0.000 lb.
Dimension - Width inch	8.31 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.63 in
Package Width	0.000 in
Dimension - D inch	7.19 in

General

Plated	N
UPC	781810079232
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	275
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810079232
UPC 14 Digit GTIN	00781810079232

Logistics

Pallet Quantity	1
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)