



GG141, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG141](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, Accommodates 3/4" IPS, 1" Rod

Features

- Accommodates IPS 3/4"
- Rod 1"

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	60 mm
Dimension - Width inch	2.38 in

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.19 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810125038
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	222
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810125038
UPC 14 Digit GTIN	00781810125038

Logistics

Minimum Pack Quantity	28
Pallet Quantity	1
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)