

GG151, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG151](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 1" IPS

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Rod Size	• 1 1/8 in • 1 1/4 in
Conductor - Copper Tube Std Size	1 IPS IPS

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	85.9 mm
Dimension - Height inch	3.38 in
Dimension - Height fraction	3-3/8 in
Package Weight	0.000 lb.
Dimension - Width mm	67 mm
Dimension - Width inch	2.63 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.31 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810260043
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	244
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260043
UPC 14 Digit GTIN	00781810260043

Logistics

Minimum Pack Quantity	16
Pallet Quantity	1
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)