



GG151SE, Mech Ground, Cu Bar/Strap/Braid/Cable to Rod/Tube

By Burndy
Catalog # [GG151SE](#)



Cast Cu Alloy Ground Connector, 1" IPS, 1-1/8" - 1-1/4" Rod, 3/8" Bolt

Features

- Cast Cu Alloy Ground Connector
- 1" IPS, 1-1/8"-1-1/4" Rod
- 3/8" Bolt

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• Rod-Size • CU Tube Std-Size
Conductor - Copper Str Size B Range	1
Conductor - Copper Tube Std Size Range	1-1/8-1-1/4
Conductor - Copper Tube Std Size	• 1-1/8 • 1-1/4

Dimensions

Package Height	0.000 in
Dimension - Height mm	85.9 mm

Dimension - Height inch	3.38 in
Package Weight	0.000 lb.
Dimension - Width mm	67 mm
Dimension - Width inch	2.63 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.31 in
Dimension - Width fraction	2-5/8 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Braid Width Max fraction	1 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810042762
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	244
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810042762
UPC 14 Digit GTIN	00781810042762

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)