



GG161SE, Mech Ground, Cu Bar/Strap/Braid/Cable to Rod/Tube

By Burndy
Catalog # [GG161SE](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	- Rod-Size - CU Tube Std-Size
Conductor - Copper Str Size B Range	1.25
Conductor - Copper Tube Std Size Range	1-1/2
Conductor - Copper Tube Std Size	1-1/2

Dimensions

Dimension - Height mm	88.9 mm
-----------------------	---------

Dimension - Height inch	3.50 in
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in
Dimension - B Length inch	1.38 in
Dimension - Width fraction	3 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Braid Width Max fraction	1 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	621945496804
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	204
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	0
UPC 14 Digit GTIN	000

Product Assets

[Catalog \[English\]](#)