

GG171, Mech Ground, Cu Bar/Strap/Braid, or Cable to Rod/Tube

By Burndy
Catalog # [GG171](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 1-1/2" Pipe, 1-5/8" - 1-7/8" Rod

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation
- Type GG connector is particularly effective for use with braid for ground rods, switch handles, fence posts and gates

Application

For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Tube Std Size	• 1-5/8 • 1-3/4 • 1-7/8
----------------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	88.9 mm
Dimension - Height fraction	3-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Dimension - B Length inch	1.38 in

Force Related

Installation Torque Recommended	240 LBS/in in-lb
---------------------------------	------------------

General

Material Type - Screw	DURIUM™ Silicon Bronze
Plated	No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810990049
Type	GG
U Bolt Type	199
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810990049
UPC 14 Digit GTIN	00781810990049

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2160
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)