



GG1715W, Mech Ground, Cu Bar/Strap/Braid/Cable to Rod/Tube

By Burndy
Catalog # [GG1715W](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• Rod-Size • CU Tube Std-Size
Conductor - Copper Str Size B Range	1.5
Conductor - Copper Tube Std Size Range	1-5/8-1-7/8
Conductor - Copper Tube Std Size	• 1-5/8 • 1-3/4 • 1-7/8

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	88.9 mm
Dimension - Height inch	3.50 in
Package Weight	0.000 lb.
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.50 in
Dimension - Width fraction	3-1/4 in
Dimension - Braid Width Max inch	1.50 in
Dimension - Braid Width Max fraction	1-1/2 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810216538
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	199
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810216538
UPC 14 Digit GTIN	00781810216538

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)