



GG171W, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG171W](#)

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, Accommodates 1-1/2" IPS, 1-5/8" to 1-7/8" Copper Rod

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - CSA Approved	No

Conductor

Conductor Type	• Rod-Size • CU Tube Std-Size
Conductor - Copper Str Size B Range	1.5
Conductor - Copper Tube Std Size Range	1-5/8-1-7/8
Conductor - Copper Tube Std Size	• 1-5/8 • 1-3/4 • 1-7/8

Dimensions

Package Height	0.000 in
Dimension - Height mm	88.9 mm
Dimension - Height inch	3.50 in

Package Weight	0.000 lb.
Dimension - Width mm	83 mm
Dimension - Width inch	3.25 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.38 in
Dimension - Width fraction	3-1/4 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Braid Width Max fraction	1 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	Y
UPC	781810207468
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	199
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810207468
UPC 14 Digit GTIN	00781810207468

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)