



GG1815, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG1815](#)

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2" Pipe, 2"-2 3/8" Rod

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation
- Type GG connector is particularly effective for use with braid for ground rods, switch handles, fence posts and gates

Application

For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Tube Std Size	• 2 • 2-1/4
----------------------------------	---



Dimensions

Package Height	0.000 in
Dimension - Height mm	108 mm
Package Weight	0.000 lb.
Dimension - Width mm	94 mm
Dimension - Width inch	3.69 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.50 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	N
Sub Brand	MECHANICAL CONNECTOR
UPC	781810260074
Type	GG
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	257
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260074
UPC 14 Digit GTIN	00781810260074

Logistics

Pallet Quantity	1728
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand