



GG1815TN, Mech Ground, Cu Bar/Strap/Braid/Cable to Rod/Tube

By Burndy
Catalog # [GG1815TN](#)

Mechanical Grounding Connector, Copper Bar/Strap/Braid/Cable to Rod/Tube, 2"-2-3/8"



Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL467
Certification - CSA Approved	No

Dimensions

Dimension - Height mm	0 mm
Dimension - Width inch	3.69 in

General

Plated	Y
UPC	621945455764
U Bolt Type	257
Material	Copper Alloy, Cast, Tin Plated
Plating Type	Tin Plated
UPC 12 Digit	621945455764
UPC 14 Digit GTIN	00621945455764

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)