



GG181W, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG181W](#)

Mechanical Ground Connector; Hot Tin Dipped, IPS 2", Rod 2" to 2-3/8", Direct Burial

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• Rod-Size • CU Tube Std-Size
Conductor - Copper Str Size B Range	2
Conductor - Copper Tube Std Size Range	2-2-1/4
Conductor - Copper Tube Std Size	• 2 • 2-1/4

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	108 mm
Dimension - Height inch	4.25 in
Package Weight	0.000 lb.
Dimension - Width mm	94 mm
Dimension - Width inch	3.69 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.38 in
Dimension - Width fraction	3-2/3 in
Dimension - Braid Width Max inch	1.00 in
Dimension - Braid Width Max fraction	1 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810163412
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	257
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810163412
UPC 14 Digit GTIN	00781810163412

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)