



GG182TN, Mech Ground, Cu Bar/Strap/Braid/Cable to Rod/Tube

By Burndy
Catalog # [GG182TN](#)

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2"-2 3/8" Pipe, 4.06 in Width. Tin Plated

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
Dimension - Height mm	111.3 mm
Package Weight	0.000 lb.
Dimension - Width mm	103 mm

Dimension - Width inch	4.06 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.75 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810416754
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	230
Material	Copper Alloy, Cast, Tin Plated
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810416754
UPC 14 Digit GTIN	00781810416754

Logistics

Minimum Pack Quantity	10
Pallet Quantity	720
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)