



GG182W, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG182W](#)



Cast Cu Alloy Ground Connector, 2" IPS, 2" - 2-3/8" Rod, Tin plated, 1/2" Bolt

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• Rod-Size • CU Tube Std-Size
Conductor - Copper Str Size B Range	2
Conductor - Copper Tube Std Size Range	2-2-1/4
Conductor - Copper Tube Std Size	• 2 • 2-1/4

Dimensions

Dimension - Height mm	111.3 mm
Dimension - Height inch	4.38 in
Dimension - Width mm	103 mm
Dimension - Width inch	4.06 in
Dimension - B Length inch	1.75 in
Dimension - Width fraction	4 in
Dimension - Braid Width Max inch	2.00 in
Dimension - Braid Width Max fraction	2 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	Y
UPC	621945552074
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	230
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	0
UPC 14 Digit GTIN	000

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)