



# GG1925, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy  
Catalog # [GG1925](#)

Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 2-1/2" Pipe, 2-1/2"-2 7/8" Rod



### Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation
- Type GG connector is particularly effective for use with braid for ground rods, switch handles, fence posts and gates

### Application

For Joining Copper Bar, Strap, Braid Or Cable To Rod Or Tube, Direct Burial Cables

### Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - UL Recognized           | No    |
| Buy American Compliant                  | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Certification - ETL                     | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance             | EX    |
| Status                                  |       |
| Certification - UL Listed Direct Burial | Yes   |
| UL Listed                               | No    |
| Certification - CSA Approved            | No    |

### Dimensions

|                       |          |
|-----------------------|----------|
| Package Height        | 0.000 in |
| Dimension - Height mm | 127 mm   |

|                           |           |
|---------------------------|-----------|
| Package Weight            | 0.000 lb. |
| Package Length            | 0.000 in  |
| Package Width             | 0.000 in  |
| Dimension - Width mm      | 116 mm    |
| Dimension - Width inch    | 4.56 in   |
| Dimension - B Length inch | 1.88 in   |

### Force Related

|                                 |                  |
|---------------------------------|------------------|
| Installation Torque Recommended | 480 LBS/in in-lb |
|---------------------------------|------------------|

### General

|                              |                           |
|------------------------------|---------------------------|
| Material Type - Screw Plated | DURIUM™ Silicon Bronze No |
| Sub Brand                    | MECHANICAL CONNECTOR      |
| Product Type                 | Mechanical                |
| UPC                          | 781810260098              |
| Type                         | GG                        |
| U Bolt Type                  | 232                       |
| Material                     | Copper Alloy, Cast        |
| Plating Type                 | Unplated                  |
| UPC 12 Digit                 | 781810260098              |
| UPC 14 Digit GTIN            | 00781810260098            |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 3 |

### Product Assets

[Catalog \[English\]](#)