



GG202SS, Mech Ground, Cu Bar/Strap/Braid/Cable to Rod/Tube

By Burndy
Catalog # [GG202SS](#)



Cast Cu Alloy Mechanical Ground Connector, 3" IPS, 3" - 3-1/2" Rod, 1/2" Bolt

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation, stainless steel hardware

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL467

Conductor

Conductor Type	• Rod-Size • CU Tube Std-Size
Conductor - Copper Str Size B Range	• 3 • 3 1/2
Conductor - Copper Tube Std Size Range	3
Conductor - Copper Tube Std Size	3

Dimensions

Package Height	0.000 in
Dimension - Height mm	162.1 mm
Dimension - Height inch	6.38 in
Package Weight	0.000 lb.

Dimension - Width mm	132 mm
Dimension - Width inch	5.19 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.88 in
Dimension - Width fraction	5-1/5 in
Dimension - Braid Width Max inch	2.00 in
Dimension - Braid Width Max fraction	2 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810356357
Material Type - Screw	Steel - Stainless
U Bolt Type	282
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810356357
UPC 14 Digit GTIN	00781810356357

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)