



GG202TN, Mech Ground, Cu Bar/Strap/Braid/Cable to Rod/Tube

By Burndy
Catalog # [GG202TN](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 3"-3-1/2" Pipe, Tin Plated

Features

- High copper alloy tin-plated ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Dimensions

Dimension - Height mm	162.1 mm
-----------------------	----------

Dimension - Width mm	132 mm
Dimension - Width inch	5.19 in
Dimension - B Length inch	1.88 in
Dimension - Width fraction	5-1/5 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	Y
UPC	781810416730
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	282
Material	Copper Alloy, Cast, Tin Plated
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810416730
UPC 14 Digit GTIN	00781810416730

Logistics

Minimum Pack Quantity	8
-----------------------	---

Product Assets

[Catalog \[English\]](#)