

GG2125, Mech Ground, Cu Bar/Strap/Braid or Cable to Rod/Tube

By Burndy
Catalog # [GG2125](#)



Mechanical Grounding Connector, Copper Bar, Strap, Braid or Cable to Rod or Tube, 3-1/2"-4" Pipe, Bolt size: 1/2"

Features

- High copper alloy ground connector for joining bar, strap, braid or cable to rod or tube
- Rated for Direct Burial in earth of concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
Dimension - Height mm	149.4 mm
Package Weight	0.000 lb.
Dimension - Width mm	144 mm

Dimension - Width inch	5.69 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	2.38 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810260128
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	263
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260128
UPC 14 Digit GTIN	00781810260128

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)