

GK1129, Cu Alloy Ground Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK1129](#)



Cast Cu Alloy Grounding Clamp, 3 Cables to Rod or Pipe, 1/2" Rod Dia, 1/4" IPS(A), 2/0 AWG Sol - 250 Kcmil Cu(AA)

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Rod Size Range	1/2 in
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Rod Size	1/2 in
Conductor - Copper Str Size B Range	0.25

Conductor - Copper Tube Std Size Range	0.5
Conductor - Copper Tube Std Size	0.5

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.50 in
Package Weight	0.000 lb.
Dimension - Width mm	84 mm
Dimension - Width inch	3.31 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.63 in
Dimension - Width fraction	3-3/8 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810233689
Type	Three Cables to Rod or Tube
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810233689
UPC 14 Digit GTIN	00781810233689

Logistics

Minimum Pack Quantity	1
Pallet Quantity	864
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)