

GK1429, Cu Alloy Ground Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK1429](#)

Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 1/2" - 3/4" Pipe, 7/8" - 1" Rod, 1/2" Stud



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining Three Equal Copper Cables To Rod Or Tube, Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rod Size Range	7/8 in-1 in
Conductor - Rod Size	• 7/8 in • 1 in
Conductor Size	2/0 AWG Sol - 250 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	93.7 mm
Dimension - Height inch	3.69 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - Width fraction	3-7/8 in
Bolt Size	1/2 in
Dimension - Width mm	97 mm
Dimension - Width inch	3.81 in
Dimension - B Length inch	1.63 in

Force Related

Installation Torque Recommended	480 LBS/in in-lb
---------------------------------	------------------

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>Three Conductor (GK)
Material Type - Screw Plated	DURIUM™ Silicon Bronze No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810233566
Type	Three Cables to Rod or Tube
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810233566
UPC 14 Digit GTIN	00781810233566

Logistics

Minimum Pack Quantity	1
Pallet Quantity	864
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)