

GK1629, Cu Alloy Ground Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK1629](#)



Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 1-1/4" Pipe, 1-3/8" - 1-1/2" Rod, 1/2" Stud

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	2/0 AWG Sol - 250 kcmil
Conductor - Rod Size	1 1/2 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	106.4 mm
Dimension - Height inch	4.19 in

Package Weight	0.000 lb.
Dimension - Width mm	113 mm
Dimension - Width inch	4.44 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.63 in
Bolt Size	1/2 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810233634
Type	Three Cables to Rod or Tube
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810233634
UPC 14 Digit GTIN	00781810233634

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)