



GK1826, Cu Alloy Ground Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK1826](#)

Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 2"; 2 3/8" Pipe, 2" - 2-3/8 ; 2 7/8" Rod, 3/8" Stud

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	#4 AWG Sol - 2/0 AWG Str
Conductor - Rod Size	• 2 in • 2 7/8 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	106.4 mm
Dimension - Height inch	4.19 in

Package Weight	0.000 lb.
Dimension - Width mm	116 mm
Dimension - Width inch	4.56 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.50 in
Bolt Size	3/8 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810233597
Type	Three Cables to Rod or Tube
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	257
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810233597
UPC 14 Digit GTIN	00781810233597

Logistics

Minimum Pack Quantity	8
Pallet Quantity	144
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)