



GK1926W, Cu Alloy Ground Clamp, 3 Cables to Rod or Pipe

By Burndy
Catalog # [GK1926W](#)



3 Copper Cables to Rod or Pipe, Accommodates 2-1/2" IPS, 2-1/2" to 2-7/8" Rod, #4 Sol - 2/0 Str Copper Cable, Tin Plated

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Copper Str Size	• 5 • 4 • 3 • 2 • 1 • 1/0 • 2/0
Conductor - Copper Str Size B Range	2.5

Conductor - Copper Tube Std Size Range	2-2-3/4
Conductor - Copper Tube Std Size	• 2 • 2-1/4 • 2-1/2 • 2-3/4

Dimensions

Package Height	0.000 in
Dimension - Height mm	127 mm
Dimension - Height inch	5.00 in
Package Weight	0.000 lb.
Dimension - Width mm	129 mm
Dimension - Width inch	5.06 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.50 in
Dimension - Width fraction	5 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	Y
UPC	781810117576
Type	Three Cables to Rod or Tube
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	266
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810117576
UPC 14 Digit GTIN	00781810117576

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)