

GK6429W, Cu Alloy Ground Clamp, 3 Cables to Rod/Pipe

By Burndy
Catalog # [GK6429W](#)



3 Copper Cables to Rod or Pipe, 3/8" IPS, 5/8"-3/4" Rod, 20 Sol-250 kcmil Copper Cable, Direct Burial, Tin Plated

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil
Conductor - Copper Str Size	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Str Size B Range	0.375
Conductor - Copper Tube Std Size Range	5/8-3/4

Conductor - Copper Tube Std Size	• 5/8 • 3/4
----------------------------------	---

Dimensions

Package Height	0.000 in
Dimension - Height mm	73.2 mm
Dimension - Height inch	2.88 in
Package Weight	0.000 lb.
Dimension - Width mm	89 mm
Dimension - Width inch	3.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.63 in
Dimension - Width fraction	3-1/2 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Plated	Y
UPC	781810079188
Type	Three Cables to Rod or Tube
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	540
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810079188
UPC 14 Digit GTIN	00781810079188

Logistics

Minimum Pack Quantity	6
Pallet Quantity	720
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)