



GKA28, Ground Connector for Cu, 1-4/0 Str

By Burndy
Catalog # [GKA28](#)

Ground Connector for Copper, Accommodates #1 Str to 4/0 Str, silicon bronze hardware



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	1 AWG-4/0 AWG
Conductor - Copper Str Size	• 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Dimensions

Dimension - Pad Width inch	0.94 in
Package Height	0.000 in
Dimension - Height mm	31.8 mm

Dimension - Height inch	1.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - B Length inch	0.81 in
Dimension - N inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.42 in
Dimension - Length Overall inch	1.94 in

Force Related

Installation Torque	275 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Trade Name	KA-LUG™
UPC	781810635209
Material Type - Screw	Steel - Stainless
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810635209
UPC 14 Digit GTIN	00781810635209

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	18

Product Assets

[Catalog \[English\]](#)