



GL2626

by Burndy
Catalog ID: GL2626

Prop 65 Notice

Mechanical Grounding Connector, 2 Copper Cables to Bar, 4 AWG (Sol.) - 2/0 AWG (Str.) (Run & Tap), 3/8" Stud.

Features: High Copper Alloy Ground Connector For Joining A Wide Range Of Two Parallel Cables To 1/4 IN Thick Bar, Two-Bolt Design, Separates Cable From Bar, One-Wrench Installation, UL467 Listed, The High Copper Alloy Cast Body And DURIUM Bolts, Nuts, And Lockwashers Make Them Suitable For Direct Burial In Concrete Or Ground, Installation Torque: 240 IN-LB, Width: 1-3/4 IN, Height: 2 IN, Bar Thickness: 1/4 IN

Product Details

General

Application	For Joining A Wide Range Of Two Parallel Copper Cables To 1/4 IN Thick Bar, Direct Burial In Concrete Or Ground
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GL
UPC	781810260012
UPC 12 Digit	7818102600122

Dimensions

Dimension - B Length inch	1.69 in
Dimension - D inch	1.94 in
Dimension - F Width Center to Center inch	1.00 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - Length Side B inch	1.88 in
Dimension - Pad Width inch	0.94 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG

Conductor - Copper Str Size Range	4 AWG-2/0 AWG
-----------------------------------	---------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)