

GL2626TN, Mech Ground Conn, 2 Copper Cables to Bar

By Burndy
Catalog # [GL2626TN](#)



Mechanical Ground Connector; 2 Copper Cables to Bar, #4 Sol - 2/0 Str, Max Bar Thickness 1/4" , Tin Plated

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG

Dimensions

Dimension - Pad Width inch	0.94 in
Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Height inch	2.00 in
Package Weight	0.000 lb.
Dimension - Width mm	44 mm
Dimension - Width inch	1.75 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.00 in
Package Width	0.000 in
Dimension - B Length inch	1.69 in
Dimension - Length Side B inch	1.88 in
Dimension - D inch	1.94 in
Dimension - Width fraction	1-3/4 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Y
UPC	781810079348
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Tin Plated
UPC 12 Digit	781810079348
UPC 14 Digit GTIN	00781810079348

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)