




GL2929T6, Mech Ground Conn, 2 Copper Cables to Bar

By Burndy
Catalog # [GL2929T6](#)



Mechanical Ground Connector; 2 Copper Cables to Bar, 2/0 AWG
Sol-250 kcmil Copper

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size Range	2/0 AWG-250 kcmil
Conductor - Copper Str Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil

Dimensions

Dimension - Pad Width inch	1.22 in
----------------------------	---------

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.25 in
Package Width	0.000 in
Dimension - B Length inch	2.22 in
Dimension - Length Side B inch	2.44 in
Dimension - D inch	2.25 in
Dimension - Width fraction	2-1/4 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810117316
Material Type - Screw	DURIUM™ Silicon Bronze
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810117316
UPC 14 Digit GTIN	00781810117316

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)