



GP1126, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP1129](#)

Cu Alloy Ground Connector, 2 Cables to Rod or Pipe, 1/2" Rod Dia., 1/4" IPS(A), 2/0 AWG Sol - 250 Kcmil Cu Cable(AA), 3/8" Bolt



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	2/0 AWG Sol - 250 kcmil
Conductor - Rod Size	1/2 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Package Weight	0.000 lb.
Dimension - Width mm	48 mm
Dimension - Width inch	1.88 in

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - B Length inch	1.75 in
Dimension - Width fraction	1-7/8 in
Bolt Size	3/8 in
Dimension - Length Overall inch	1.94 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810260524
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	271
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810260524
UPC 14 Digit GTIN	00781810260524

Logistics

Minimum Pack Quantity	10
Pallet Quantity	2160
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)