



GP114C, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP114C](#)

Cu Alloy Ground Connector, 2 Cables to Rod or Pipe, 1/2" Rod Dia., 1/4" IPS(A), #8 Sol - #4 Str AWG Cu Cable(AA), 3/8" Bolt



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	#8 AWG Sol - #4 AWG Str
Conductor - Rod Size	1/2 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Package Weight	0.000 lb.
Dimension - Width mm	48 mm
Dimension - Width inch	1.88 in

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - B Length inch	1.50 in
Dimension - Width fraction	1-7/8 in
Bolt Size	3/8 in
Dimension - Length Overall inch	1.31 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810260500
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	271
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810260500
UPC 14 Digit GTIN	00781810260500

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)