



GP1429, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP1429](#)

Mechanical Grounding Connector, 2 Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 1/2" - 3/4" Pipe, 1" Rod, 3/8" Stud.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Application

For Joining A Range Of Parallel Copper Cables Perpendicular To Rod, Pipe Or Column, Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rod Size	1 in
Conductor Size	2/0 AWG Sol - 250 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Package Weight	0.000 lb.
Package Length	0.000 in



Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - Width fraction	2-3/8 in
Bolt Size	3/8 in
Dimension - Width mm	60 mm
Dimension - Width inch	2.38 in
Dimension - B Length inch	1.75 in
Dimension - Length Overall inch	1.94 in

Force Related

Installation Torque Recommended	240 LBS/in in-lb
---------------------------------	------------------

General

Material Type - Screw	DURIUM™ Silicon Bronze
Plated	No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810260593
Type	GP
U Bolt Type	249
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810260593
UPC 14 Digit GTIN	00781810260593

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)