



GP1629W, Mech Ground Conn, 2 Cables to Rod/Pipe, Tin Plated

By Burndy
Catalog # [GP1629W](#)

2 Copper Cables to Rod, Pipe, or Column, Accommodates 1-1/4" IPS, Tube 1-4/8" OD, 2/0 Sol-250 kcmil Copper Cable, Tin Plated



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	2/0 AWG Sol - 250 kcmil
Conductor - Rod Size Range	1 3/8" - 1 1/2"

Dimensions

Package Height	0.000 in
Dimension - Height mm	88.9 mm
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Dimension - Width inch	3.00 in

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	49 mm
Dimension - B Length inch	1.88 in
Dimension - Width fraction	3 in
Bolt Size	3/8 in
Dimension - Length Overall inch	1.94 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	Y
UPC	781810485613
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	204
Material	Tin Plated Copper Alloys
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810485613
UPC 14 Digit GTIN	00781810485613

Logistics

Minimum Pack Quantity	8
Pallet Quantity	108
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)