



GP1826, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP1826](#)

Mechanical grounding connector, 2" Pipe Size, 2" Rod Size, 4 SOL - 2/0 STR Wire Size, 240 LBS/in Installation Torque.



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	#4 Sol AWG - 2/0 Str AWG
Conductor - Rod Size	2 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	111.3 mm
Package Weight	0.000 lb.
Dimension - Width mm	94 mm
Dimension - Width inch	3.69 in
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall mm	43 mm
Dimension - B Length inch	2.75 in
Dimension - Width fraction	3-11/16 in
Bolt Size	3/8 in
Dimension - Length Overall inch	1.69 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810079171
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	257
Material	Copper Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810079171

Logistics

Pallet Quantity	1
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)