



GP2226, Mech Ground Conn, 2 Cables to Rod or Pipe

By Burndy
Catalog # [GP2226](#)

Mechanical grounding connector, 4 AWG Solid - 2/0 AWG Stranded, 4" Pipe, 4" Rod, 240 LBS/in Installation Torque.



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	#4 Sol AWG - 2/0 Str AWG
Conductor - Copper Solid Size Range	4-3/0
Conductor - Copper Str Size Range	5 AWG - 2/0 AWG
Conductor - Rod Size	4 in

Dimensions

Package Height	0.000 in
Dimension - Height mm	162.1 mm
Package Weight	0.000 lb.

Dimension - Width mm	148 mm
Dimension - Width inch	5.81 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	43 mm
Dimension - B Length inch	4.50 in
Dimension - Width fraction	5-13/16 in
Bolt Size	3/8 in
Dimension - Length Overall inch	1.69 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Plated	N
UPC	781810001653
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	261
Material	Copper Alloy
Plating Type	Unplated
UPC 14 Digit GTIN	00781810001653

Logistics

Minimum Pack Quantity	4
Pallet Quantity	600
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)