



BURNDY

GP64528G1, Mech Ground, 2 Cables to Round or Square Pedestal

By Burndy

Catalog # [GP64528G1](#)

Mech Ground Connector, 2 Cables to Round or Square Pedestal, 3/4"-1" Round, 3/4"-7/8" Square, #4 Solid-4/0 Stranded



Features

- 3/8" Bolt size
- Conductor Run #4 Sol- 4/0 AWG Str
- 1 or 2 conductor
- Copper alloy
- Accepts 3/4-1" round pedestal or 3/4-7/8" square pedestal

Specifications

Standards - RoHS Compliance Status

EX

Buy America(n) Qualified

Contact Manufacturer
UL Listed
Yes
Certification - CSA Approved
No

Conductor

Conductor Size
#4 AWG Sol - 4/0 AWG Str
Conductor Type
CU C Str-Size
Conductor - Copper Str Size Range
4 AWG - 4/0 AWG

Dimensions

Package Height
0.000 in
Dimension - Height mm
0 mm
Package Weight
0.000 lb.
Dimension - Width mm
60 mm
Dimension - Width inch
2.38 in
Package Length
0.000 in
Package Width
0.000 in
Dimension - L Length Overall mm
43 mm
Dimension - B Length inch
1.50 in
Bolt Size
3/8 in
Dimension - Length Overall inch
1.69 in

Force Related

Installation Torque Recommended in-lb
240 LBS/in

General

Plated
N
Pedestal Type

- Round
- Square

UPC
781810657508
U Bolt Type
UB222
Material
Copper Alloy, Cast
Plating Type
Unplated
UPC 12 Digit
781810657508
UPC 14 Digit GTIN
00781810657508

Logistics

Minimum Pack Quantity
1
Pallet Quantity
2400
Carton Quantity
12

Product Assets



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY-GP64528G1-SPEC-EN | REV 5/2026