



GQ2929, Copper Ground Connector, 2/0 AWG Str-250 kcmil

By Burndy
Catalog # [GQ2929](#)

Cu Ground Connector, 2/0 AWG Str - 250 kcmil Cu, 6" IPS, Cable to Tube



Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	2/0 AWG Str - 250 kcmil
Conductor Type	• CU Tube Std-Size • CU C Str-Size
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Dimensions

Package Height	0.000 in
Dimension - Height mm	87.4 mm
Dimension - Height inch	3.44 in
Package Weight	0.000 lb.

Dimension - Width mm	70 mm
Dimension - Width inch	2.75 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	152 mm
Dimension - Width fraction	2-3/4 in
Bolt Size	1/2 in
Dimension - Length Overall inch	6.00 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Plated	N
UPC	781810260616
Material Type - Screw U Bolt Type	DURIUM™ Silicon Bronze • 247 • 291
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810260616
UPC 14 Digit GTIN	00781810260616

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)