

**GRC34, Mechanical Ground Rod Clamp,
Cable to Rod**

By Burndy
Catalog # [GRC34](#)

Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 8
AWG (Sol.) - 1/0 AWG (Str.), 3/4" Ground Rod, 3/8" Stud

Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets

Application

For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And
Stainless Steel Ground Rods, Direct Burial Applications In Earth And
Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rod Size	3/4 in
Conductor Size	#8 AWG Sol - 1/0 AWG Str
Conductor - Copper Solid Size	8 AWG
Range	
Conductor Type	• Rod-Size • CU C Solid-Size
Conductor - Copper Str Size Range	8 AWG - 1/0 AWG

Dimensions

Package Height	4.720 in
----------------	----------



Dimension - Height mm	62.7 mm
Dimension - Height inch	2.40 in
Package Weight	13.220 lb.
Package Length	7.250 in
Package Width	6.250 in
Dimension - Width mm	28 mm
Dimension - Width inch	1.09 in
Dimension - B Length inch	0.65 in
Dimension - Length Side B inch	0.65 in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>Acorn Clamps (GRC/GRL)
Material - Hardware Plated	Silicon Bronze No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810230985
Type	GRC, High Strength
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810230985
Hardware Type	Silicon Bronze
UPC 14 Digit GTIN	00781810230985

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)