



GRC58, Mechanical Ground Rod Clamp, Cable to Rod

By Burndy
Catalog # [GRC58](#)

Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 10 AWG (Sol)- 1 AWG (Str), 5/8" Drive Rod, 3/8" Stud

Features

- Rated for Direct Burial in earth or concrete
- UL 467 Listed for the US and Canadian Markets

Application

For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	RUS
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	#10 AWG Sol - #1 AWG Str
Conductor - Copper Solid Size Range	10 AWG
Conductor Type	• Rod-Size • CU C Solid-Size
Conductor - Copper Str Size Range	12 AWG-1 AWG



Conductor - Rod Size	5/8 in
----------------------	--------

Dimensions

Package Height	4.750 in
Dimension - Height mm	55.6 mm
Dimension - Height inch	2.18 in
Package Weight	12.630 lb.
Dimension - Width mm	24 mm
Dimension - Width inch	0.95 in
Package Length	7.100 in
Package Width	6.500 in
Dimension - B Length inch	0.57 in
Dimension - Length Side B inch	0.63 in

General

Plated	N
Material - Hardware	Silicon Bronze
Sub Brand	MECHANICAL CONNECTOR
UPC	781810230961
Type	GRC, High Strength
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810230961
Hardware Type	Silicon Bronze
UPC 14 Digit GTIN	00781810230961

Logistics

Pallet Quantity	10000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)