



GRL5, Ground Rod Clamp, Light Duty, Cable to Rod

By Burndy
Catalog # [GRL5](#)

Light Duty Mechanical Ground Rod Clamp, Copper #10 AWG -#2 AWG, 5/8" Ground Rod

Features

- UL467 Listed
- Acceptable for Direct Burial in earth or concrete

Application

For Direct Burial

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rod Size	5/8 in
Conductor Size	#2 AWG - #10 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG

Dimensions

Package Height	0.000 in
----------------	----------



Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>Acorn Clamps (GRC/GRL)
Plated	No
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810051825
Type	GRL, Light Duty
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810051825
UPC 14 Digit GTIN	00781810051825

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)