

GRL6, Ground Rod Clamp, Light Duty, Cable to Rod

By Burndy
Catalog # [GRL6](#)

Light Duty Mechanical Ground Rod Clamp, Copper #2 AWG - #10 AWG, 3/4" Rod Size

Features

- UL467 Listed
- Acceptable for Direct Burial in earth or concrete

Application

For Direct Burial

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Certification - UL Listed Direct	Yes
Burial	
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	#2 AWG - #10 AWG
Conductor - Copper Str Size Range	10 AWG - 2 AWG
Conductor - Rod Size	3/4 in

Dimensions

Package Height	0.000 in
----------------	----------



Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	No
Product Family	Grounding and Bonding Connectors>Copper Mechanical Grounding Connectors>Cable(s) to Ground Rod/Pipe/Tube (GAR/GD/GK)>Acorn Clamps (GRC/GRL)
Sub Brand	MECHANICAL CONNECTOR
Product Type	Mechanical
UPC	781810051832
Type	GRL, Light Duty
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810051832
UPC 14 Digit GTIN	00781810051832

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)