



GX294C, Mech Grounding Connector, Cable Cross Connection

By Burndy
Catalog # [GX294C](#)

Cast Cu Alloy Ground Connector, 2/0 AWG Sol - 250 Kcmil(A),
#8 Sol - #4 Str AWG(AA), 1/2" Rod Dia., Bronze H/W



Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Str Size B	• 9 • 8 • 7 • 6 • 5 • 4
Conductor - Copper Str Size A Range	1/0-250
Conductor - Copper Solid Size A	• 2/0 • 3/0 • 4/0
Conductor - Copper Solid Size B	• 8 • 7 • 6 • 5 • 4 • 3
Conductor - Copper Solid Size A Range	2/0-4/0

Conductor - Copper Solid Size B Range	2/0-4/0
Conductor Type	• CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B
Conductor - Copper Str Size B Range	9-4
Conductor - Copper Tube Std Size	0.5

Dimensions

Package Height	0.000 in
Dimension - Height mm	69.9 mm
Dimension - Height inch	2.75 in
Dimension - Height fraction	2-3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Width fraction	1-7/8 in
Dimension - Width mm	48 mm
Dimension - Width inch	1.88 in
Dimension - Length Overall inch	1.88 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze N
UPC	781810260678
U Bolt Type	222
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810260678
UPC 14 Digit GTIN	00781810260678

Logistics

Minimum Pack Quantity	12
Pallet Quantity	900
Carton Quantity	25



A Hubbell brand