



GX3434, Mech Grounding Connector, Cable Cross Connection

By Burndy
Catalog # [GX3434](#)

Cast Cu Alloy Ground Connector, 300 - 500 Kcmil(A), 300 - 500 Kcmil(AA), 3/4" Rod Dia., Bronze H/W

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	• 300 • 350 • 400 • 450 • 500
Conductor - Copper Str Size B	• 300 • 350 • 400 • 450 • 500
Conductor - Copper Str Size A Range	300-500
Conductor Type	• CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B
Conductor - Copper Str Size B Range	300-500



Conductor - Copper Tube Std Size 0.75

Dimensions

Package Height	0.000 in
Dimension - Height mm	108 mm
Dimension - Height inch	4.25 in
Dimension - Height fraction	4-1/4 in
Package Weight	0.000 lb.
Dimension - Width mm	67 mm
Dimension - Width inch	2.63 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	67 mm
Dimension - Width fraction	2-5/8 in
Dimension - Length Overall inch	2.62 in

Force Related

Installation Torque Recommended in-lb 480 LBS/in

General

Plated	N
UPC	781810260739
Material Type - Screw	DURIUM™ Silicon Bronze
U Bolt Type	256
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810260739
UPC 14 Digit GTIN	00781810260739

Logistics

Minimum Pack Quantity	4
Pallet Quantity	270
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)