



GX4C4C, Mech Grounding Connector, Cable Cross Connection

By Burndy
Catalog # [GX4C4C](#)



Cast Cu Alloy Ground Connector, #8 Sol - #4 Str AWG(A), #8 Sol - #4 Str AWG(AA), 3/8" Rod Dia., Bronze H/W

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	• 9 • 8 • 7 • 6 • 5 • 4
Conductor - Copper Str Size B	• 8 • 7 • 6 • 5 • 4
Conductor - Copper Str Size A Range	9-4
Conductor - Copper Solid Size A	• 8 • 7 • 6 • 5 • 4 • 3
Conductor - Copper Solid Size B	• 8 • 7 • 6 • 5 • 4

Conductor - Copper Solid Size A Range	• 3 8-3
Conductor - Copper Solid Size B Range	8-3
Conductor Type	• CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B
Conductor - Copper Str Size B Range	8-4
Conductor - Copper Tube Std Size	0.375

Dimensions

Package Height	0.000 in
Dimension - Height mm	47.8 mm
Dimension - Height inch	1.88 in
Dimension - Height fraction	1-7/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	41 mm
Dimension - Width fraction	1-5/8 in
Dimension - Width mm	41 mm
Dimension - Width inch	1.63 in
Dimension - Length Overall inch	1.62 in

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Material Type - Screw Plated	DURIUM™ Silicon Bronze N
UPC	781810986295
U Bolt Type	327
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810986295
UPC 14 Digit GTIN	00781810986295

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)



A Hubbell brand