



HSB100FR, Heat Shrink Tubing PVC, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB100FR](#)



1" ID Min (Exp), 1/2" ID Max (Rec), 1/0-4/0 Flex, PVC, Flame Retardant, 25-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	4/0AWG - 300kcmil
Conductor Range	#1/0 AWG to #4/0 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Length	300 in
Width	1 in
Height	1 in
Dimensions	300 in x 1 in x 1 in

General

Sub Brand	HEAT SHRINK
Type	HS-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride
UPC	781810265741

Logistics

Minimum Pack Quantity	1
Carton Quantity	10
Pallet Quantity	360

Product Assets

[Catalog \[English\]](#)