



HSB100FR100, Heat Shrink Tubing PVC, Thin, FR, Black

By Burndy
Catalog # [HSB100FR100](#)

1" ID Min (Exp), 1/2" ID Max (Rec), 1/0-4/0 Flex, PVC, Flame Retardant, 100-Foot Reel



Features

- Heat Shrink Tubing, 1.00" ID Min (Exp), 0.50" ID Max (Rec), 1/0-4/0
- PVC
- Fire Retardant
- Thin Wall, Black
- 100 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#1/0 AWG to #4/0 AWG
Conductor Size	4/0AWG - 300kcmil

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	1 in
Height	1 in
Length	1200 in
Dimensions	1200 in x 1 in x 1 in

General

Material	Polyvinyl chloride
UPC	781810265758
Color	Black

Logistics

Minimum Pack Quantity	2
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)