



HSB100FR100FT, Heat Shrink Tubing PVC, Thin, FR, Black

By Burndy
Catalog # [HSB100FR100FT](#)

1" ID Min (Expanded), 1/2" ID Max (Recovered), 1/0-4/0 Flex, PVC, Flame Retardant, 100-Foot Reel



Features

- Heat Shrink Tubing, 1.00" ID Min (Exp), 0.50" ID Max (Rec), 1/0-4/0 Flex
- PVC
- Fire Retardant
- Thin Wall, Black
- 100 Foot Reel
- 600 V

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Configuration

Connector TypeTHIN WALL TUBES/REELS

Dimensions

Width	1 in
Height	1 in
Length	1200 in
Dimensions	1200 in x 1 in x 1 in

General

Material	Polyvinyl chloride
UPC	781810038550

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[Catalog \[English\]](#)