



# HSB100T300PF, Heat Shrink Tubing PVC, Thin, Black

By Burndy  
Catalog # [HSB100T300PF](#)

1" ID (Expanded), 1/2" ID Min. (Recovered), 2/0-300, Polyolefin, 25-Foot Reel

## Features

- Heat Shrink Tubing, 1" ID Min (Exp), 0.5" ID Max (Rec)
- 2/0 - 300
- Polyolefin Thin Wall Black
- 600 V
- 25 Foot Reel

## Specifications

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| UL Listed                          | No  |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |

## Conductor

|                 |                      |
|-----------------|----------------------|
| Conductor Range | #2/0 AWG - 300 Kcmil |
| Conductor Size  | 2/0AWG - 300kcmil    |

## Configuration

|                |                |
|----------------|----------------|
| Connector Type | THIN WALL REEL |
|----------------|----------------|

## Dimensions

|            |                      |
|------------|----------------------|
| Width      | 1 in                 |
| Height     | 1 in                 |
| Length     | 300 in               |
| Dimensions | 300 in x 1 in x 1 in |

## General

|          |                         |
|----------|-------------------------|
| Material | Cross-linked Polyolefin |
| UPC      | 781810213971            |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[Catalog \[English\]](#)