



HSB110H4PF25, Heat Shrink Tubing, Heavy, Black

By Burndy
Catalog # [HSB110H4PF25](#)

1.10" ID Min (Expanded), .35" ID Max (Recovered), 1-3/0, Polyolefin, Thick Wall, 4" Lengths, 25 Pieces

Features

- Heat Shrink Tubing, 1.10" ID Min (Exp), 0.35" ID Max (Rec), 1-3/0
- Polyolefin, Thick Wall
- Black, Shrink Ratio 3:1, 1500V

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Range	#1 AWG to #3/0 AWG
-----------------	--------------------

Current

Voltage Rating	1500 V
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Product Type	Polyolefin Thick Wall Heat Shrink
UPC	781810454060
Material	Polyolefin

Logistics

Number of Pieces in Package	25
Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	625

Product Assets

[Catalog \[English\]](#)