



HSB110H6PF5, Heat Shrink Tubing, Heavy, Black

By Burndy
Catalog # [HSB110H6PF5](#)

1.10" ID Min (Expanded), .4" ID Max (Recovered), 1-3/O, Polyolefin, Thick Wall, 6" Lengths, 5 Pieces

Features

- Heat Shrink Tubing, 1.10" ID Min (Exp), 0.40" ID Max (Rec)
- 1-3/O, Polyolefin, Thick Wall
- Black, Shrink ratio 3:1, 1500V
- UL486D Listed for Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	1AWG - 3/OAWG
Conductor Range	#1 AWG to #3/O AWG

Configuration

Connector Type	HEAVY WALL TUBES
----------------	------------------

Current

Voltage Rating	1500 V
----------------	--------

Dimensions

Package Height	14.000 in
Package Weight	7.580 lb.
Package Length	16.100 in
Package Width	16.450 in

General

UPC	781810214824
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	5
Number of Pieces in Package	5
Pallet Quantity	4500
Carton Quantity	125

Product Assets

[Catalog \[English\]](#)